

Quick & Easy

# Simplified Tensile Tester

## PT-3000DG-P

**Grasping the weld strength and meeting the requirements are essential when high welding quality is demanded!**

Are you sure your weld is strong enough? How can you explain how good your weld is?-----This Simplified Tensile Tester can be your solution.



Place a spotwelded sample on the machine.



Pull it until the welded surface comes apart.




The shear strength is shown as a numeral. Press the print button to print the result.




Print out the result.

Space saving design!



Printer attached.

Spacer is included for testing nuts.



**PT-3000DG-P**

Model	PT-3000-DG-P
Max. Measuring capacity	30kN(Measurable range: 2kN to 30kN)
Accuracy	±10%
Load indication	Digital
Clamping method	Top/Bottomclamps
Pressing method:	Manual Lever (With hydraulic jack)
Test Sample dimensions:	JIS 3136 for single point (30mmx100mm)
Weight:	68kg
Dimensions:	H800xW460xD400mm, desktop

Koyo gikken inc.  
4020-4 Tana Chuo-ku Sagamihara Kanagawa 252-0244 JAPAN  
Tel: 042-760-4306 Fax: 042-760-4309

**koyo giken**  
www.koyogikken.co.jp

2016.04.01